



Polaris™ PR53AP Sanitary Probe Process Refractometer



The Vaisala Polaris PR53AP sanitary probe process refractometer is designed for food and beverage, dairy and brewery industry customers, and OEMs to measure liquid concentrations, such as Brix, in applications such as jam cookers and mixing tanks. 3-A and EHEDG certifications ensure that all hygienic demands and safety requirements are met. The long probe can withstand high process temperatures and its design enables flexible installations directly to kettles, cookers, vessels, and tanks.

Features

- Reliable optical concentration measurements with refractive index
- Brix, Total Solids, Oechsle, Baume, Plato, and more than 500 concentration curves
- 3-A and EHEDG certified
- Sanitary and tank bottom flange couplings
- Measurement not affected by bubbles, particles, suspended solids, or color
- Indigo520-compatible
- Built-in 4–20 mA and Modbus RTU outputs

Benefits

The optical measurement is based on the refractive index (RI). The RI can be measured from practically any liquid, and it responds to dissolved material. The long probe allows representative measurement in tanks and hot processes, such as jam cooking.

The outstanding long-term stability provides years of accurate, continuous, fast, and stable measurement for concentration of sugar (Brix) and various other chemical concentrations directly in the process stream. Inline process refractometers are easy to install and have no moving parts that require regular maintenance.

The PR53AP continues the success of the Vaisala K-PATENTS® process refractometer series. Based on 40 years of experience and continuous development, the PR53 family is the latest generation of digital process refractometers.

Safe for sanitary applications

The product design welcomes both cleaning-in-place (CIP) and sterilization-in-place (SIP) systems. Stainless-steel wetted parts, PTFE and sapphire, are suitable to be in direct contact with the process, and traceability ensures safety. Stainless steel is easy to maintain and keep clean. The long probe with common tank bottom flanges enables installation depths of up to 170 mm. The flush mount option allows installation in tanks with scrapers or mixers.

Brix and beyond

Brix is a common measurement unit in the food, dairy, and beverage processing industries. Measurements can also be shown in total solids, Oechsle, Baume, or Plato. Other measurement units include concentration of sucrose, gelatin, lactulose, and hydrogen peroxide. The refractometer comes pre-configured with the selected concentration curve.

Wash system

Most applications do not need wash systems due to the self-cleaning effect: the shear force of the process flow keeps the measurement point clean. For the most demanding applications, the powerful wash system ensures correct measurement when process conditions are sticky.

Plug and play to Indigo


The refractometer can be interfaced directly, or it can be connected to a Vaisala Indigo520 transmitter. It provides access to features such as data storage, graphical interface, and analog and digital interface. The Indigo520 transmitter is required when the application or the installation position requires washing, to control the process. Changing settings, measurement parameters, or other servicing updates can be done directly from the Indigo520, or through a USB cable using Vaisala software.

Technical data


Measurement performance

Refractive index	
Measurement range	1.32–1.53 nD (Corresponds to 0–100 °Bx)
Accuracy	±0.00014 nD (0.1 °Bx) ¹⁾
Repeatability	±0.00002 nD ²⁾
Resolution	±0.000015 nD
Response time T ₆₃ with default damping	10 s ³⁾
Measurement cycle	1 / s
Long-term stability	Max. 0.1 % full scale / a
Temperature	
Accuracy at 20 °C (68 °F)	±0.3 °C (0.54 °F) ¹⁾
Sensor class	F0.15 IEC 60751
Temperature coefficient	±0.002 °C / °C

- 1) Accuracy specified with respect to calibration reference, including non-linearity, hysteresis at +20 °C.
- 2) Repeatability, confidence level k=2, including random noise, at T_a = +20 °C, with standard low-pass filtering.
- 3) With standard low-pass filtering.



PR53AP, depth 170 mm process temperature (indicative)




PR53AP, depth 42 mm and 66 mm process temperature (indicative)

Operating environment

Process parameters	
Process temperature	-40 ... +150 °C (-40 ... +302 °F) ¹⁾
Design temperature	+180 °C (356 °F) ²⁾
Design pressure	40 bar ³⁾
Operating environment	
Storage temperature	-40 ... +65 °C (-40 ... +149 °F)
Operating temperature	-40 ... +60 °C (-40 ... +140 °F)
Maximum operating altitude	2000 m (approx. 6500 ft)
Operating humidity	0–100 %RH
Storage humidity	0–100 %RH, non-condensing
UL 50E (NEMA) rating	Type 4X
IP rating	IP66 IP67

- 1) -40 ... +130 °C (-40 ... 266 °F) EPDM gasket, -40... +150 °C (-40 ... +302 °F) PTFE gasket
- 2) Maximum momentary temperature peak.
- 3) Maximum at +20 °C (68 °F), operating pressure to the clamp rating pressure.



PR53AP process pressure

Inputs and outputs

Supply	
Operating voltage	24 V DC nominal (9–30 V DC)
Power consumption	Less than 1 W
Protection class	3, PELV
Outputs	
Output parameters	RI, temperature, concentration, quality factor
Analog outputs	
mA	Sourcing, isolated, NAMUR NE 43, configurable
mA range	3.8–20.5 mA
Loop impedance	Max. 600 Ω
Accuracy of analog outputs at +20 °C	±0.1 % of full scale (±0.00002 RI)
Digital outputs	
Digital output	RS-485, non-isolated
Maximum cable run	300 m (approx. 1000 ft) (digital)
Supported protocol	Modbus RTU
Connectors	
External connectors	1 × M12 M 4 pins, A-coded ¹⁾ 2 × M16×1.5 cable gland, Cable D 5–10 mm / Adapter for conduit entry M16×1.5 ²⁾ / NPT ½"

- 1) For USB2 adapter and Insight software, see www.vaisala.com/insight.
- 2) Conduit hub is not compatible with PR53 Safe-Drive system.

Compliance

Electromagnetic compatibility (EMC)	EN 61326-1, industrial environment
Safety	IEC/EN/UL 61010-1
Pressure	CRN all territories, ASME BPVC Sec VIII Div. 1 Ed. 2021
Material compliance	FDA 21 CFR 177.150, 177.2600, 177.1550 EC 1935/2004 EC 2023/2006, GMP EU 10/2011
Compliance marks	CE, China RoHS, RCM, UKCA
Vibration and shock	Tested according to IEC 60068-2
Listing marks	MET listed (US and Canada)

Sanitary compliance

Hygienic design	3-A 46-04 EHEDG ¹⁾
Compliance marks	3-A, EHEDG ²⁾
Biocompatibility	USP Class VI <88>, 70 °C
ADI free (Animal Derived Ingredients)	Yes

¹⁾ Excluding tank bottom flange.

²⁾ For EHEDG compliant installation, use 2.5" / 4" sanitary gasket.

Mechanical specifications

Wetted parts	
Sensor head	EN 1.4435 BN2 (AISI 316L) ¹⁾
Wash nozzle	EN 1.4404 (AISI316L) ¹⁾ EPDM gasket ²⁾
Surface roughness	Ra 0.8 µm
Prism	Sapphire monocrystalline, 99.996 % Al ₂ O ₃ ²⁾
Prism gasket	Modified PTFE ³⁾
Sanitary gasket 2.5" / 4"	EPDM ²⁾
Tank bottom gasket MT4 DN25/1T for tank bottom flange	EPDM ²⁾
Tank bottom flange	AISI316L ¹⁾
Welding ferrule	EN 1.4435 (AISI 316L) ^{1) 4)}
Non-wetted parts	
Housing	EN 1.4404 (AISI 316L)
Screws, TX20, torque 2.0 Nm	EN 1.4404 (AISI 316L)
Cable gland	EN 1.4305 (AISI 303) HUMMEL 1.693.1600.50
Dummy plug	EN 1.4305 (AISI 303) AGRO 8717.96.08.70
Conduit hub	EN 1.4404 (AISI 316L) Vaisala, DRW257718, M16×1.5 / NPT ½ in
M12 connector	Gland, EN 1.4305 (AISI 303) Contacts, CuZn with Ni/Au plating Phoenix Contact, 1405233, M12/4(M), A, 4×0.34 mm ² , TPE, 0.5 m Carrier, PA 6.6
Sanitary clamp 2.5" / 4"	EN 1.4301 (AISI 304) ²⁾
Cable	2×2×0.5 mm ² (AWG 21), PUR jacket, black 10 m multistrand, with ferrules Flame-retardant acc. to IEC 60332-1-2, FT1, VW1
Weight	3.6–4.2 kg (7.94–9.26 lb)

¹⁾ Material certificate included.

²⁾ Manufacturer's declaration included.

³⁾ ADI free, FDA 21 C.F.R 177.1550, 3A Sanitary Standard, USP Class VI <88>, 70 °C.

⁴⁾ 3-A certificate, EHEDG certificate.


Calibration accessories

Item	Item code
Verification kit 1.33, 1.37, 1.42, 1.47, 1.52	280380SP
Calibration kit 1.32, 1.33, 1.35, 1.36, 1.37, 1.38, 1.40, 1.42, 1.45, 1.47, 1.50, 1.52, 1.53, 1.57	278292SP
High-range special kit 1.42, 1.47, 1.53, 1.57, 1.60, 1.62, 1.67, 1.72	278293SP
Sample holder and cover	278295SP

Accessories

Item	Item code
USB adapter for service port, for Insight service software (see www.vaisala.com/insight)	USB2
Instrument cable, 2×2×0.5 mm ² (AWG 21), PUR jacket, grey, open ends, 10 m (33 ft) Flame-retardant acc. to IEC 60332-1-2, FT1, VW1	CBL211266-10M
Instrument cable, 2×2×0.5 mm ² (AWG 21), PUR jacket, grey, open ends, 30 m (98 ft) Flame-retardant acc. to IEC 60332-1-2, FT1, VW1	CBL211266-30M
Instrument cable, 2×2×0.5 mm ² (AWG 21), PUR jacket, grey, open ends, 50 m (164 ft) Flame-retardant acc. to IEC 60332-1-2, FT1, VW1	CBL211266-50M
Cooling cover	ASM214675SP


Options for PR53AP



Dimensions of PR53AP Sanitary 2.5", depth 170 mm

Mounting accessories for PR53AP Sanitary 2.5", depth 170 mm


Item
Welding ferrule, 2.5"
Sanitary clamp 2.5"
Blind flange 2.5"
Sanitary gasket 2.5", EPDM
Sanitary gasket 2.5", PTFE/steel, Combifit VOE-2034 (EHEDG)



Dimensions of PR53AP Sanitary 4", depth 66 mm

Mounting accessories for PR53AP Sanitary 4", depth 66 mm


Item
Welding ferrule, 4"
Sanitary clamp 4"
Blind flange 4"
Sanitary gasket 4", EPDM
Sanitary gasket, 4", PTFE/steel, Combifit VOE-2036 (EHEDG)



Dimensions of PR53AP Sanitary 2.5", depth 42 mm

Mounting accessories for PR53AP Sanitary 2.5", depth 42 mm


Item
Welding ferrule, 2.5"
Sanitary clamp 2.5"
Blind flange 2.5"
Sanitary gasket 2.5", EPDM
Sanitary gasket, 2.5", PTFE/steel, Combifit VOE-2034 (EHEDG)



Dimensions of PR53AP Sanitary 4", depth 170 mm, with wash nozzle

Mounting accessories for PR53AP Sanitary 4", depth 170 mm, with wash nozzle

Item
Welding ferrule, 4"
Sanitary clamp 4"
Blind flange 4"
Sanitary gasket 4", EPDM
Sanitary gasket, 4", PTFE/steel, Combifit VOE-2036 (EHEDG)




Dimensions of PR53AP Sanitary 4", depth 170 mm


Mounting accessories for PR53AP Sanitary 4", depth 170 mm

Item
Welding ferrule, 4"
Sanitary clamp 4"
Blind flange 4"
Sanitary gasket 4", EPDM
Sanitary gasket, 4", PTFE/steel, Combifit VOE-2036 (EHEDG)

Options for PR53AP



Dimensions of PR53AP tank bottom flange, depth 170 mm



Dimensions of PR53AP tank bottom flange, flush mounted


Mounting accessories for PR53AP tank bottom flange, depth 170 mm and tank bottom flange, flush mounted

Item

Tank bottom welding flange

Tank bottom blind flange

Gasket MT4 DN25/1T EPDM



Dimensions of PR53AP tank bottom welding flange